

Crystal Unit

YSX530GA Glass Sealed



Applications

- Industrial Control
- Consumer Electronics

Features

- Dimensions: 5.00 x 3.20 x 1.2 mm
- Standard Frequency: 8 ~ 54MHz

- 2 Pads SMD Glass Sealed Crystal Units
- Contains Pb in Sealing Glass Exempted by ROHS Directive

Specifications (规格参数)

Item	Symbol	Specifications
Nominal Frequency Range (额定频率范围)	f_nom	8 ~ 54MHz
Vibration Mode (震动模式)	-	AT Fundamental
Load Capacitance (负载电容)	CL	10pF, 20pF, or specify
Frequency Tolerance (频率偏差) (at 25°C)	f_tol	±10ppm, ±20ppm, or specify
Frequency Versus Temperature Characteristics (频率-温度特性)	f_tem	±20ppm, or specify
Operating Temperature (工作温度)	T_use	-20~+70°C, -40~+85°C, or specify
Storage Temperature (储存温度)	T_stg	-55~+125°C
Shunt Capacitance (静态电容)	C0	5pF Max
Level of Drive (激励电平)	DL	10~300μW Max (100μW typical)
Aging (老化) (at 25°C)	f_age	±3ppm/year Max

Equivalent Series Resistance (等效串联电阻(ESR))

YSX530GA	
8 ~ 16MHz	80Ω Max
16 ~ 25MHz	40~60Ω Max
25 ~ 54MHz	30~40Ω Max

Dimensions and Recommended Land Pattern (外观尺寸及推荐焊盘)

Dimensions (Unit: mm)	Recommended Land Pattern (Unit: mm)
<p>Top View</p> <p>Side View</p> <p>Bottom View</p>	<p>Top View Crystal Connection</p> <p>Top View Suggested Layout</p>