




Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS  
Rated Current:2.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:400V AC/DC  
Insulation Resistance:800MΩ Min  
Operation Temperature:-40°C to +105°C

Contact Material:Brass  
Contact Plating:Au or Sn Over Ni  
Insulator Material:Polyester(UL94V-0)  
Resistance To Soldering Heat:  
245°C ±5°C, 10s(PBT insulator)  
260°C ±5°C, 10s(PA6T&PA9T&LCP insulator)



### Ordering Information

XDJN 200 - \* - N - W - \* - \*\*

No. of Rows  
1=Single Row  
2=Dual Row

No. of Pins  
03-32Pin

Type  
Z=弯针  
W=弯针  
S=直插

Length  
英寸

Contact Plating  
G0:Gold Flash  
G1:0.8u' Gold  
G2:3u' Gold  
G3:5u' Gold  
G4:10u' Gold  
G5:15u' Gold  
G6:30u' Gold  
S0:Gold Flash/Tin  
S1:1in

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	筒牛2.00 双排 弯针 塑高5.7	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDJN200-2-N-W-5.7-G0	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						