



SPECIFICATIONS
 Rated Current:3.0AMP
 Contact Resistance:20mΩMax
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩMin
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Resistance To Soldering Heat:
 245°C±5°C, 10s(PBT insulator)
 260°C±5°C, 10s(PA6T insulator)

Ordering Information

XDNJ 254 - * - N - * - * - ** - * - *

No. of Rows 2=Dual Row	No. of Pins 03-32 Pin	Type Z=直针 W=弯针 S=插指	Length 型高	Contact Plating G0:Gold Flash G1:0.8μ Gold G2:3.0μ Gold G3:5.0μ Gold G4:10.0μ Gold G5:15.0μ Gold G6:30.0μ Gold S0:Gold Flash/In S1:In	Color 默认=Black G=Grey	Latch Type 默认=Long Latch S=Short Latch N=Without Latch
---------------------------	--------------------------	------------------------------	--------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------	-----------------------------------------------------------------

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	牛角座 2.54 直针 长耳扣	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDNJ254-2-N-Z-27.8-G0	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						