


SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20m ΩMax
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M ΩMin
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating: Au or Sn Over Ni
Insulator Material: Polyester(UL94V-0)
Resistance To Soldering Heat:
245°C±5°C, 10s(PBT insulator)
260°C±5°C, 10s(PA6T&PA9T&LCP insulator)

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	牛角座 2.54 弯针 长耳扣	版本 REV.	A
			X.XX ±0.10	比例 SCALE	产品料号 PART NO.	XDNJ254-2-N-W-27.8-G0	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					