



SPECIFICATIONS:

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 30mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Material: Nylon 66,UL94V-0 (White)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	4.60	2.30	10P	18.00	20.60	14.30
3P	4.00	6.60	2.30	11P	20.00	22.60	14.30
4P	6.00	8.60	4.30	12P	22.00	24.60	14.30
5P	8.00	10.60	6.30	13P	24.00	26.60	14.30
6P	10.00	12.60	6.30	14P	26.00	28.60	14.30
7P	12.00	14.60	6.30	15P	28.00	30.60	14.30
8P	14.00	16.60	6.30	16P	30.00	32.60	14.30
9P	16.00	18.60	6.30				

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit: mm
 Scale: 4:1
 Sheet: 1 of 1
 DRAWN: Chengbiao Ye
 CHK'D: Djankui Wan
 APPR: Jack Yin

TITLE: 2.00mm PITCH HOUSING

REV	DESCRIPTION	DATE
A2	CHANGE THE DRAWING	2023.06.09
A1	MODIFY DRAWING	2016.08.08
A0	NEW RELEASE	2009.05.10

General Tolerances:
 x,xx±0.25
 x.xxx±0.20
 x,xxxx±0.15
 ANGLES ±1°

THIRD ANGLE PROJECTION
 DRAWING NO. A2008H-XP
 REV A2