



RoHS



- 技术指标 (Technical Index):
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
 2. 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
 3. 额定电流 (Rated current): 0.5A
 4. 额定电压 (Rated voltage): 50V, AC/DC (=等效).
 5. 耐电压 (Withstand Voltage): 500V, AC/minute.
 6. 接触电阻 (Contact resistance): $\leq 50\text{m}\Omega$.
 7. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.

Model No.	Pin	DIM A	DIM B	DIM C
FPC-1.0LS-04PH25	4	3.00	5.03	11.10
FPC-1.0LS-05PH25	5	4.00	6.03	12.10
FPC-1.0LS-06PH25	6	5.00	7.03	13.10
FPC-1.0LS-07PH25	7	6.00	8.03	14.10
FPC-1.0LS-08PH25	8	7.00	9.03	15.10
FPC-1.0LS-09PH25	9	8.00	10.03	16.10
FPC-1.0LS-10PH25	10	9.00	11.03	17.10
FPC-1.0LS-11PH25	11	10.00	12.03	18.10
FPC-1.0LS-12PH25	12	11.00	13.03	19.10
FPC-1.0LS-13PH25	13	12.00	14.03	20.10
FPC-1.0LS-14PH25	14	13.00	15.03	21.10
FPC-1.0LS-15PH25	15	14.00	16.03	22.10
FPC-1.0LS-16PH25	16	15.00	17.03	23.10
FPC-1.0LS-17PH25	17	16.00	18.03	24.10
FPC-1.0LS-18PH25	18	17.00	19.03	25.10
FPC-1.0LS-19PH25	19	18.00	20.03	26.10
FPC-1.0LS-20PH25	20	19.00	21.03	27.10
FPC-1.0LS-21PH25	21	20.00	22.03	28.10
FPC-1.0LS-22PH25	22	21.00	23.03	29.10
FPC-1.0LS-23PH25	23	22.00	24.03	30.10
FPC-1.0LS-24PH25	24	23.00	25.03	31.10
FPC-1.0LS-25PH25	25	24.00	26.03	32.10
FPC-1.0LS-26PH25	26	25.00	27.03	33.10
FPC-1.0LS-27PH25	27	26.00	28.03	34.10
FPC-1.0LS-28PH25	28	27.00	29.03	35.10
FPC-1.0LS-29PH25	29	28.00	30.03	36.10
FPC-1.0LS-30PH25	30	29.00	31.03	37.10
FPC-1.0LS-31PH25	31	30.00	32.03	38.10
FPC-1.0LS-32PH25	32	31.00	33.03	39.10
FPC-1.0LS-33PH25	33	32.00	34.03	40.10
FPC-1.0LS-34PH25	34	33.00	35.03	41.10
FPC-1.0LS-35PH25	35	34.00	36.03	42.10
FPC-1.0LS-36PH25	36	35.00	37.03	43.10
FPC-1.0LS-37PH25	37	36.00	38.03	44.10
FPC-1.0LS-38PH25	38	37.00	39.03	45.10
FPC-1.0LS-39PH25	39	38.00	40.03	46.10
FPC-1.0LS-40PH25	40	39.00	41.03	47.10

适用扁平线 (Applicable Flat Cable)

适用线路板 (PCB LAYOUT)

NO.	Name	Number	Qty	Materil	Remarks
①	Soldering lug		1	Phosphor Bronze	Plating Sn
③	Cover		1	LCP	Black
②	Terminal			Phosphor Bronze	Plating Sn
④	Housing		1	LCP	Off White

YUANDI® Yuandi Electronics Co, Ltd

design	date	name	FPC CONNECTOR
Review	date	model	FPC-1.0LS-□□PH25
Approved	date	Drawing number:	

1.0型卧式上接(H=2.5)抽屉式 1.0 Type Horizontal Top Connection (H=2.5) Drawer Type