


SEC.:A-A



SEC.:B-B


Wire Range	Insulation Diameter	Reel Q'ty
AWG #28~#32	1.00 (.039) MAX.	15,000 PCS.

Ordering Code:

CI44 T01 1 P P 0
 ① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Type: T01= AWG #28~ #32
- ③ Plating: 1= 2.03μm(80μ") Min. Tin over 0.76μm(30μ") Nickel
- ④ Material: P= Phosphor Bronze
- ⑤ Plating method: P=Post Plating
- ⑥ Option: 0= Standard

RoHS Compliant

⑥	Eric	12/29-23'	ECNT123325/ECRT123089		DATE	UNIT: mm / inch	TITLE: 1.25mm(.049") CRIMP CLIP TERMINAL	 瀚荃股份有限公司 CviLux Corporation
⑤	Karen	9/20-16'	ECNT116213/ECRH116035	DRAWN BY: Eric	12/29-23'	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:	
④	Enya	8/12-13'	ECNT113029	ENGINEER: Eric	12/29-23'	.X ± 0.20/.008 X' ± 1"	FINISH:	
③	Bill	01/03/08	ECR08002-0/ECN08001	CHECKED BY: Eisley	12/29-23'	.XX ± 0.10/.004 .X' ±	DRAWING NO. CI4402SL PART NO. CI44T011PPO	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	12/29-23'	.XXX ± 0.05/.002 .XX' ±	SCALE 9 / 1 SHEET 1 OF 1	

CviLux Corp
 2024/01/06
 ISSUED