



注記  
NOTES

- 1. 材料および仕上げ(めっき仕様) : TABLE 1 参照  
MATERIAL AND FINISHES : SEE TABLE 1
- 2. 適合製品及び各種仕様書は下記参照のこと  
REFER TO BELOW TABLE ABOUT RELATED PRODUCTS AND VARIOUS SPECIFICATIONS.

適合製品及び各種仕様書  
APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

適合ハウジング APPLICABLE HOUSING	212132 SERIES
適合嵌合相手 MATE WITH	212134 SERIES
製品仕様書 PRODUCT SPECIFICATION	2121320000-PS/PS/000
梱包仕様書 PACKING SPECIFICATION	2040179200-SPK/PS/000
コネクタ取扱説明書 APPLICATION SPECIFICATION	2166940000-AS/PS/0000

製品嵌合図は嵌合相手図面参照のこと  
MATING VIEW: REFER TO "MATE WITH" PART DRAWING.

1 TABLE 1

部品 PART	材質 MATERIAL	
ターミナル TERMINAL	銅合金 COPPER ALLOY	
	下地めっき UNDER PLATING	ニッケルめっき(下地) : 0.5 micro-meters MIN NICKEL (UNDER PLATING)
	接点部 CONTACT	金めっき : 0.1 micro-meters MIN GOLD PLATING

Ø0.6 - 0.7 mm	AWG #28-30	リール REEL	2040175021	連鎖状 CHAIN
絶縁被覆外径範囲 INS. RANGE	適合電線範囲 WIRE RANGE	梱包形態 PACKAGING	発注番号 ORDER No.	端子形状 FORM

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS mm	SCALE NTS	CURRENT REV DESC:		<b>molex</b>		
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 643659				
ANGULAR TOL	± 3.0 °	DRWN: SNAKAMURA08		PRODUCT CUSTOMER DRAWING		
4 PLACES	± 0.2	CHK'D: SAKIYAMA		DOCUMENT NUMBER		
3 PLACES	± 0.2	APPR: KOMURAKAMI		2040175001-SD		DOC TYPE
2 PLACES	± 0.2	INITIAL REVISION:		PSD		DOC PART
1 PLACE	± 0.2	DRWN: SNAKAMURA08		000		REVISION
0 PLACES	± 0.2	APPR: KOMURAKAMI		A		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
		A3-SIZE	204017	SEE TABLE	GENERAL	1 OF 1