


Wire Range	Insulation Diameter	Reel Q'ty
AWG #28~#30	0.70 (.028) MAX.	15,000 PCS.


Ordering Code:

CI63 T01 2 P P 0  
 ① ② ③ ④ ⑤ ⑥


- ① Series No.
- ② Type: T01= AWG #28~ #30
- ③ Plating: 2= Gold Flash plated over 0.76μm(30μ") Nickel
- ④ Material: P= Phosphor Bronze
- ⑤ Plating method: P= Post Plating
- ⑥ Option: 0= Standard




SECTION A-A



SECTION B-B



SECTION C-C



RoHS Compliant

SYM	NAME	DATE	REVISIONS	APPROVED BY:	DATE	UNIT: mm / inch	TITLE:	DRAWING NO.	PART NO.	SCALE	SHEET	OF	1
4						mm / inch	1.20MM CRIMP TERMINAL	CI6303SA	CI63T012PP0	6 / 1	1	OF	1
3						TOLERANCE UNLESS OTHERWISE SPECIFIED							
2						.X ± 0.30/.012							
1						.XX ± 0.20/.008							
						.XXX ± 0.10/.004							

CVILUX CORP  
 2015.08.27  
 ISSUED

瀚荃股份有限公司  
 CviLux Corporation