




Material: Nylon 66 UL 94V-0
Color Nature



Ordering Code:

CI52 ** S 0000
① ② ③ ④

- ① Series No.
- ② No. of Circuits
- ③ S= Connector housing
- ④ Other option: 0000= Standard

Circuits	Dimension	
	A	B
2	3.96(.156)	8.1(.319)
3	7.92(.312)	12.1(.476)
4	11.88(.468)	15.8(.622)
5	15.84(.624)	19.8(.780)
6	19.80(.780)	23.8(.937)
7	23.76(.935)	27.7(1.091)
8	27.72(1.091)	31.7(1.248)
9	31.68(1.247)	35.6(1.402)
10	35.64(1.403)	39.6(1.559)
11	39.60(1.559)	43.6(1.717)
12	43.56(1.715)	47.5(1.870)



Halogen-Free
RoHS Compliant

CVILUX CORP
2022.09.08
ISSUED

④					DATE	UNIT: mm / inch	TITLE: 3.96MM(.156") CRIMP TERMINAL HOUSING	瀚荃股份有限公司 CviLux Corporation
③				DRAWN BY: Sun	9/2-22'	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:	
②				ENGINEER: Sun	9/2-22'	.X ± 0.38 / .015 X' ± 1"	FINISH:	DRAWING NO. CI5201SC PART NO. CI52**S0000
①	Sun	9/02-22'	ECNT122167	CHECKED BY: Eisley	9/5-22'	.XX ± 0.25 / .010 .X' ±		SCALE 3 / 1
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	9/5-22'	.XXX ± 0.10 / .004 .XX' ±		