



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #323039
PIDG R OFS 22-16COM22-18MIL 6




TE Part #ZPF000000000100854
DMC-MD 20 B




TE Part #ZPF000000000015291
DMC-M 20-22 AN




TE Part #4-2176422-4
TLRP 2512 3.0W R150 1% 25PPM 4K RL




TE Part #33526M11-08PB
RECP ASSY




TE Part #33525M11-08SA
PLUG ASSY




TE Part #33526M11-08PN
RECP ASSY



TE Part #605705-31
CONT PIN



TE Part #WM16BF06-09SN-990A
PLUG ASSY



TE Part #605704-ZZ
CONT SKT.SIZE 24.

Documents

Product Drawings

[PIN INSERT, 16-02 CABLE APPLIED](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2226454-1_E_c-2226454-1-e.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2226454-1_E_c-2226454-1-e.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2226454-1_E_c-2226454-1-e.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DMC-M Series Single Module EN4165

English

Product Specifications

Application Specification

English