



| | | | 1 | | |
|--|----------------|-----------------|----------|-----------|--|
| | Part Number: | | DRAWN | 5/23/2018 | |
| | MOOG | 4002-3 | CJ | 3/23/2016 | |
| | יסטטוייו י | | CHECKED | 5/23/2018 | |
| | | | C.H. | | |
| | Description: | M' l | APPROVED | 5/23/2018 | |
| | Electret Conde | nser Microphone | C.E. | 3/23/2010 | |

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




Side View



Bottom View



Schematic



| Items | Specifications | Conditions | | | | | | |
|---|-----------------|------------|-----|---|------------|----------|--|--|
| Directivity | Omnidirectional | | | | | | | |
| Sensitivity | -40 ± 2 | dB | | | | | | |
| Frequency Range | 50 ~ 16,000 | Hz | | REVISION HISTORY | | | | |
| Rated Voltage | 2 | V | REV | DESCRIPTION | DATE | APPROVED | | |
| Voltage Range | 2 ~ 10 | V | | Released from Engineering | 10/21/2013 | J.S. | | |
| Output Impedance | 2,200 | Ω | 1 | Updated to new drawing template | 5/23/2018 | C.E. | | |
| Max. Rated Current | 0.5 | mA | | NOTES | | | | |
| Storage Temperature | -25 ~ +70 | °C | | All dimensions are in mm unless otherwise noted | | | | |
| Operating Temperature | -20 ~ +60 | °C | | 2) All tolerances are ± 0.2 mm unless otherwise noted | | | | |
| Signal to Noise Ratio | 60 | dB | | 3) All parts meet RoHS | | | | |
| Mount Type | Thru Hole | | | 4) Subject to change or redrawn without notice | | | | |
| Connection Method | PC Pins | | | | | | | |
| 4 3 Additional considerations can be found at www.dbunlimitedco.com/technical-articles. | | | | | | | | |