



|  |                                |                  | 1        |           |  |
|--|--------------------------------|------------------|----------|-----------|--|
|  | Part Number:                   |                  | DRAWN    | 8/10/2017 |  |
|  | MOOO                           | 4204-1           | CJ       | 0/10/2017 |  |
|  | 141009                         |                  | CHECKED  | 8/14/2017 |  |
|  |                                |                  | P.D.     |           |  |
|  | Description:<br>Electret Conde | enser Microphone | APPROVED | 8/14/2017 |  |
|  |                                |                  | C.E.     |           |  |

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View




## Side View



## **Bottom View**





Additional considerations can be found at www.dbunlimitedco.com/technical-articles.

|   | Items                 | Specifications  | Conditions |                  |   |            |          |  |
|---|-----------------------|-----------------|------------|------------------|---|------------|----------|--|
|   | Directivity           | Omnidirectional |            |                  |   |            |          |  |
|   | Sensitivity           | -42 ± 2         | dB         |                  |   |            |          |  |
| A | Frequency Range       | 50 ~ 16,000     | Hz         | REVISION HISTORY |   |            |          |  |
|   | Rated Voltage         | 4.5             | V          | REV              | DESCRIPTION   | DATE       | APPROVED |  |
|   | Voltage Range         | 1 ~ 10          | V          |                  | Released from Engineering   | 10/21/2013 | J.S.     |  |
|   | Output Impedance      | 2,200           | Ω          | 1                | Add Pin Dimensions, update to new template, voltage range changed | 8/14/2017  | C.E.     |  |
|   | Max. Rated Current    | 0.5             | mA         |                  | NOTES 1   |            |          |  |
|   | Storage Temperature   | -25 ~ +70       | °C         |                  | All dimensions are in mm unless otherwise noted                   |            |          |  |
|   | Operating Temperature | -20 ~ +60       | °C         |                  | 2) All tolerances are ± 0.5 mm unless otherwise noted             |            |          |  |
|   | Signal to Noise Ratio | 60              | dB         |                  | 3) All parts meet RoHS  |            |          |  |
|   | Mount Type            | Thru Hole       |            |                  | 4) Subject to change or redrawn without notice                    |            |          |  |
|   | Connection Method     | PC Pins         |            |                  |   |            |          |  |