


## **TOP VIEW**



## SIDE VIEW



## **BOTTOM VIEW**



Specifications			Notes		Revision History						
Description	Value	Unit	Notes		Version	Description			Date	Approved	
Directivity	Omnidirectional		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S	
Technology	Electret Condenser		2) All parts meet RoHS								
Sensitivity	-42	(dB)									
Frequency Range	50 ~ 16,000	(Hz)									
Rated Voltage	2	(V)									
Impedance	2,200	(Ohm)									
Connection Method	Solder Pads										
Voltage Range	2~10	(V)									
Max Rated Current	0.5	(mA)			Drawn by	Date	Checked by	Date	Approved by	Date	
Minimum Signal to Noise Ratio	>60	(dB)			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013	
Operating Temperature	-20 ~ +60	°C		Electrot Condensor Misro	Microphono		MO064202-3				
Storage Temperature	-25 ~ +70	°C		Electret Condenser Microphone		10004202-3					

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.