
THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, MITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

■ 2005, Projects Unlimited Inc.

SPECIFICATIONS

REVISIONS						
LTR	DESCRIPTION	DATE	APPROVED			
_	RELEASED FROM ENGINEERING	11/18/14				

PARAMETERS	AMETERS VALUES	
DIRECTIVITY	OMNI	_
SENSITIVITY	-38±3	dB
STANDARD OPERATING VOLTAGE	2	Vdc
MAX OPERATING VOLTAGE	10	Vdc
CURRENT CONSUMPTION (MAX)	0.5	mA
IMPEDANCE	2.2	k0hm
SIGNAL TO NOISE RATIO (MIN.)	>58	dB
TERMINAL	LEAD WIRE	_
INTERNAL CAPACITOR	10&33	pF



NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.
- 4. PART IS IP67 RATED

UNLESS OTHERWISE SPECIFIED: ALL PURCHASES ARE SUBJECT TO THE PUI UDIO TERMS AND CONDITIONS SALE FOUND A http://www.puiaudio.com/pdf/terms_conditions.pdf (paper copy available upon request).

IMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

audio nc a projects unlimited company
--

3541 Stop Eight Road Dayton, Ohio 45414

APP	ROVALS	DATE	N	
DRAWN	M.L.	11/14	SIZE	IV
CHECKED	M.L.	11/14	Ä	
APPROVED	B.R.	11/14	SCALE	: N.T.S.

DRAWING NO. SIZE

TOW-1538L-LW100-R SHEET

TOW-1538L-LW100-R.DW(