



SIDE VIEW



## **BOTTOM VIEW**



	Specifications		Notes		Revision History				
Description	Value	Unit	Notes		Version	Description			Date
Directivity	Noise Cancelling		1) All dimensions are in mm	1	Release	d from Engineering		2/9/2014	
Technology	Electret Condenser		2) All parts meet RoHS						
Sensitivity	-54	(dB)							
Frequency Range	100 ~ 10,000	(Hz)							
Rated Voltage	1.5	(V)							
Impedance	680	(Ohm)							
Connection Method	Solder Pads								
Voltage Range	1.0 ~ 10.0	(V)							
Max Rated Current	0.5	(mA)			Drawn by	Date	Checked by	Date	Approved by
Min. Signal to Noise Ratio	55	(dB)			G.W.	10/31/2013	C.E.	1/16/2014	J.S.
Operating Temperature	-10 ~ +50	°C	Floatrot Condoncor Mic		nhono	MN095401-1			
Storage Temperature	-20 ~ +60	°C	DB UNLIMITED	Electret Condenser Micro	Mone   MINU954U1-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.

Approved J.S.

Date 2/9/2014