TOP VIEW			SIDE VIEW		BOTTOM VIEW					
-			5.2±0.			5±0.05 A	$\left \right\rangle$	Term.1 - Term.2		
Specifications			Neter		Revision History					
Description	Value	Unit	Notes		Version				Date	Approved
Directivity	Omnidirectional		1) All dimensions are in mm u	1	Released from Engineering			10/21/2013	J.S	
Technology	Electret Condenser		2) All parts meet RoHS							
Sensitivity	-40	(dB)								
Frequency Range	50 ~ 16,000	(Hz)	_							
Rated Voltage	1.5	(V)								
Impedance	2,200	(Ohm)								
Connection Method	PC Pins									
Voltage Range	1.5 ~ 10	(V)					T	ī		
Max Rated Current	0.5	(mA)			Drawn by	Date	Checked by	Date	Approved by	Date
Minimum Signal to Noise Ratio	>60	(dB)			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Operating Temperature Storage Temperature	-20 ~ +60 -25 ~ +70	°C °C			ophone	MO064001-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.