


			1		
	Part Number:		DRAWN	2/21/2016	
	MO064202-2		CJ	3/31/2016	
	יסטטויו	1202-2	CHECKED	4/1/2016	
			P.D.		
	Description:	N4'	APPROVED	4/1/2016	
	Electret Conde	enser Microphone	J.S.	4/1/2010	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




Solder Pads

Connection Method

Side View



Bottom View



Items	Specifications	Conditions						
Directivity	Omnidirectional							
Sensitivity	-42	dB		REVISION HISTORY				
Frequency Range	50 ~ 16,000	Hz	REV	DESCRIPTION	DATE	APPROVED		
Rated Voltage	2	V		Released from Engineering	10/21/2013	J.S.		
Voltage Range	1 ~ 10	V	1	Updated height and Template	4/1/2016	P.D.		
Output Impedance	2,200	Ω	2	Corrected Signal to Noise Ratio	5/24/2017	C.E.		
Max. Rated Current	0.5	mA	NOTES					
Storage Temperature	-20 ~ +60	°C		All dimensions are in mm unless otherwise noted				
Operating Temperature	-10 ~ +50	°C		2) All tolerances are ± 0.5 mm unless otherwise noted				
Signal to Noise Ratio	>58	dB		3) All parts meet RoHS				
Mount Type	Flush Mount		4) Subject to change or redrawn without notice					