

1 2 3 4 5 6 7 8 9

G

F

E

D

C

B

A



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60seconds
 (260° C for 5 seconds)



Code Description

XY-200-FH-1-XX-43-S-28-24-GO-A
 (1) (2) (3) (4) (5) (6) (7) (8) (9) (10)

(1) Pin Spacing: 200=2.0mm
 (2) Product Name: FH=Female Header
 (3) No. of Rows: 1=Single Row ; 2=Dual Row
 (4) No. of Pins Per Row: 1~40
 (5) Insulator Material Height: 43=4.3mm; 72=7.2mm
 (6) Connector Type: S=Straight; R=Right; Angle M=SMT
 (7) Connector Material Length: 24=2.4mm; 28=2.8mm
 (8) Insulator Material Width: 40=4.0mm 45=4.5mm
 (9) Contact Plating: GO=Gold Flash; AU10=Au 1.0u"
 (10) Insulator Material Option:
 A=BK-PA6T; B=BK-PA46; C=KB-LCP; S=Special



RECOMMEND P. C. B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)



深圳市虹成电子有限公司

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00

UNLESS OTHERWISE SPECIFIED TOLERANCE
 X : ±0.3 X° : ±5°
 X.X : ±0.2 X.X° : ±1°
 X.XX : ±0.1 X.XX° : ±0.5°

DRAWING NAME: 2.0FH 1x12Pin H4.3 DIP

SIZE	A4	SCALE	N:1	PRODUCT NO.	HC-PM200-1x12-4.3HZ
REV	A	UNIT	mm	PROJECT	PAGE 1/1

CHECKED: LI BEI LIN 12/03/07 CHECKED: / / APPROVED: / /

1 2 3 4 5 6 7 8 9