

16381.2 GSM-ANTENNA-EXTERNAL- GSM+GPS-SMA-3M



Combined cellular/GPS antenna with omni-directional, SMA round connector (GSM/UMTS) and R-SMA round connector (GPS), connection cable length 3 m

RAL: 9005

Business data

| | |
|--|-------------------------------------|
| Article number | <u>16381.2</u> |
| Article name | GSM-ANTENNA-EXTERNAL-GSM+GPS-SMA-3M |
| GTIN (EAN) | 4044211207816 |
| Packaging unit | 1 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 155 g |
| Weight per piece (including packaging) | 158 g |
| Unit of weight | G |
| Customs number | 85291069 |
| Country of origin | EU |
| Product description | GSM-GPS antenna |
| Colour | Black |

16381.2 GSM-ANTENNA-EXTERNAL- GSM+GPS-SMA-3M

Technical data

Dimensions

| | |
|---------------------|---------|
| Length | 81.3 mm |
| Width | 81.3 mm |
| Height | 29.6 mm |
| Installation height | 14.6 mm |
| Drill hole diameter | 13 mm |

Connection data

| | |
|---------------------|-------------------------------|
| Plug-in connector | SMA-Male |
| GPS frequency | 1575,42 ± 1 MHz |
| Antennengewinn max. | 1 dBi / 2 dBic |
| GSM frequency | 800, 850, 900, 1900, 2100 MHz |
| Impedance | 50 Ohm |

Materials

| | |
|---------------------------|--------|
| Material | ABS |
| Working temperature, min. | -40 °C |
| Working temperature, max. | 85 °C |

Further technical data

| | |
|---------------|-----------------|
| Mounting type | External, screw |
| Cable length | 3 m |
| Antenna shape | Puck |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

16381.2 GSM-ANTENNA-EXTERNAL- GSM+GPS-SMA-3M

Media

16381.2 GSM-ANTENNA-EXTERNAL- GSM+GPS-SMA-3M

Accessories

##INVERSE##CONTA-ELECTRONICS



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>16369.2</u> | GSM-PRO2-GPS | 4044211207748 | 1 ST |



Compact reporting system for mobile networks to monitor analogue and digital values as well as remotely switch relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|---------------|---------------|----------------|
| <u>16408.2</u> | GSM-PRO2E-GPS | 4044211219024 | 1 ST |