



# 698-960 & 1710-2700 MHz LTE WORLD BAND ANTENNA

Part Numbers: 2372112-1, 2372112-2

2372112-5, 2372112-6

#### FEATURES & BENEFITS


- Adhesive backing on the FPC simplifies mounting within the device
- Omnidirectional coverage
- Efficient design reduces power usage
- No matching components required
- Ground-plane independent design


#### **SPECIFICATIONS**

Frequency Range (MHz)	698-960 1710-2700					
VSWR	< 2.6:1 < 3.0:1					
Efficiency	38% 52%					
Average Gain	-4.8dBi -3.7dBi					
Peak Gain	-0.2dBi	0.2dBi				
Power Handling	10 Watt cw					
Feed Point Impedance	50 ohms unbalanced					
Polarization	Linear					
Size	65 mm x 15 mm x 0.2 mm					
Weight	< 2.0 g					
Mounting	Adhesive Tape					
Mating Connector	MHF and MHF4L type, refer to page5					
Cable (coaxial)	1.13mm Dia. Refer to page5					
Operating Temperature	-40 to +85°C					
Storage Temperature	-40 to +85°C					
Hazardous Materials	A certificate of conformance is available from the product page on TE website.					



### **RF DATA**







Data measured in free space and on plastic device enclosure

829

2205

0% **└** 698

1710


960

2700

Frequency(MHz)




### RADIATION PATTERN




Data measured in free space and on plastic device enclosure



### **KEEP OUT AREA**






#### **NOTES**

- 1. Antenna designed to be mounted on plastic cover.
- 2. Area in blue indicates Keep Out Area.
- 3. For more information please call TE.

Dimension: mm Diagrams is not to scale

## **DIMENSIONS**

## (Refer to Page5 for dimension "A")






## MATING COMPONENTS TO PART NUMBER AND DIMENSIONS

2372112-1	150	5.91	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2372112-2	100	3.94	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2372112-5	150	5.91	1.13	MHF4L-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2372112-6	100	3.94	1.13	MHF4L-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
PART	MM	INCH	CABLE (OD)	CONNECTOR TYPE	PART NUMBER	IMAGE
NUMBER	NUMBER CABLE LENGTH(A) m		mm	(ON CABLE)	MATING COMPONENTS	

#### **PACKAGING**



#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

#### te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

01/2022