

16173.2 GSM-ANTENNA-EXTERNAL-SMA-10M



GSM UMTS antenna with omni-directional characteristic, SMA round plug, Connecting cable length: 10 m

Business data

| | |
|--|------------------------------|
| Article number | <u>16173.2</u> |
| Article name | GSM-ANTENNA-EXTERNAL-SMA-10M |
| GTIN (EAN) | 4044211187019 |
| Packaging unit | 1 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 457 g |
| Weight per piece (including packaging) | 480 g |
| Unit of weight | G |
| Customs number | 85291069 |
| Country of origin | NL |
| Product description | GSM antenna |

16173.2 GSM-ANTENNA-EXTERNAL-SMA-10M

Technical data

Dimensions

| | |
|---------------------|-------|
| Length | 80 mm |
| Width | 80 mm |
| Height | 45 mm |
| Installation height | 23 mm |
| Drill hole diameter | 17 mm |

Connection data

| | |
|---------------------|-------------------------------|
| Plug-in connector | SMA-Male |
| Antennengewinn max. | 1 dBi |
| GSM frequency | 800, 850, 900, 1900, 2100 MHz |
| Impedance | 50 Ohm |

Materials

| | |
|---------------------------|---------|
| Material | Nylon 6 |
| Working temperature, min. | -40 °C |
| Working temperature, max. | 85 °C |

Further technical data

| | |
|---------------|-----------------|
| Mounting type | External, screw |
| Cable length | 10 m |
| Antenna shape | Puck |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Media

16173.2 GSM-ANTENNA-EXTERNAL-SMA-10M

Accessories

##INVERSE##CONTA-ELECTRONICS



Compact reporting system for mobile networks to monitor analogue and digital values, and to remotely switch relay outputs, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC.

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>16368.2</u> | GSM-PRO2 | 4044211207731 | 1 ST |



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>16369.2</u> | GSM-PRO2-GPS | 4044211207748 | 1 ST |



Compact signaling system for mobile networks to monitor analog and digital values as well as remotely switch relay outputs, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC.

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>16407.2</u> | GSM-PRO2E | 4044211219017 | 1 ST |



Compact reporting system for mobile networks to monitor analogue and digital values as well as remotely switch relay outputs, incl. GSM positioning, Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|---------------|---------------|----------------|
| <u>16408.2</u> | GSM-PRO2E-GPS | 4044211219024 | 1 ST |



Compact reporting system for mobile networks, for monitoring analogue and digital values and remotely switching relay outputs. Mounting type: Mounting rail TS 35, Supply voltage range: 10 - 30 VDC

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>16099.2</u> | GSM-PRO | 4044211151560 | 1 ST |