





50W 2-8GHZ 20DB DIRECTIONAL COUPLER

PAGE 1/2 ISSUE 06-12-19A SERIES COUPLER PART NUMBER R433514700

**Scale 1:1** 



**Scale 2:1** 



All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **23,8400** g







50W 2-8GHZ 20DB DIRECTIONAL COUPLER

PAGE <b>2/2</b>	ISSUE 06-12-19A	SERIES COUPLER	PART NUMBER <b>R433514700</b>
-----------------	-----------------	-------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency operating range:	2 – 8 GHz
Impedance :	50 Ω
VSWR: - Main Line	1.25 max.
- Coupled Line	1.25 max.
Nominal Coupling :	20 dB
Coupling Precision:	± 1 dB
Insertion Loss:	0.4 dB max.
Directivity:	20 dB mini
Frequency Sensitivity:	± 0.4 dB
Average Power at 25°C	50W
Peak Power at 25°C	3000W

## **MECHANICAL CHARACTERISTICS**

Connector type:	SMA female per MIL-C 39012
Coaxial Termination:	SMA, 50 Ω, 1W

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperatur	e:   -40°C / +100°C
Storage temperatur	e: -40°C / +100°C