

Technical Data Sheet


DP3T Ramses SMA 3GHz Failsafe Indicators 12Vdc Diodes Pins terminals

PAGE 1/2	ISSUE 09-03-2	I SERIE : DP3T	PART NUMBER : R585322030
RF CHARACT	ERISTICS		
Frequer Impedar	cy range	: 0 - 3 GHz : 50 Ohms	
impedai	Ce	. 50 011115	
Frequer	cy (GHz) DC -	3	
VSWR r			
	n loss max 0.20 d min 80 dB		
Isolation Average	power (*) 240 V		
	CHARACTERISTICS		
LLLOIMOAL	SHARAOTERIOHOO		
Actuator		: FAILSAFE	
Nominal current **		∶ 500 mA ∶ 12V (10.2 te	- 13)/)
Actuator voltage (Vcc) Terminals		-	; (250°C max. / 30 sec.)
Indicator rating		: 1 W / 30 V /	
MECHANICAL	CHARACTERISTICS		
Connect Life	ors	: SMA femal : 10 million o	e per MIL-C 39012
Switching Time***		: < 10 ms	
Constru	tion	: Splashproo	of
Weight		∶ < 100 g	
	ITAL CHARACTERISTICS	<u>}</u>	
	ITAL CHARACTERISTICS	<u>5</u> ∶ -40°C to +8	5°C
Operatir			۶۰۲
Operatir	g temperature range	∶ -40°C to +8	
Operatir Storage	g temperature range temperature range	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	g temperature range temperature range power at 25°C per RF Pa	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C	ig temperature range temperature range power at 25°C per RF Pa ±10%)	∶ -40°C to +8 ∶ -55°C to +8	۶۰۲
Operatir Storage (* Average (** At 25° C (*** Nominal	ig temperature range temperature range power at 25°C per RF Pa ±10%) voltage ; 25° C)	: -40°C to +8 ∶ -55°C to +8 th)	۶۰۲



Technical Data Sheet

DP3T Ramses SMA 3GHz Failsafe Indicators 12Vdc Diodes Pins terminals



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.