



			1		
	rt Number:		DRAWN	44 (45 (2047	
	CMOE	0508-2	CJ	11/16/2017	
	SIMZSU		CHECKED	11/17/2017	
			P.D.		
	Description: Dynamic	c Speaker	APPROVED	11/17/2017	
			C.E.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Items	Specifications	Conditions						
Sound Pressure Level	90	dB (@ 10cm)						
Resonant Frequency	600	Hz						
Frequency Range	600 ~ 5,000	Hz		REVISION HISTORY				
Nominal Power	1	W	REV	DESCRIPTION	DATE	APPROVED		
Max. Power	1.2	W		Released from Engineering	11/17/2017	C.E.		
Impedance	8	Ω	· ·	NOTES				
Cone Material	PEEK			All dimensions are in mm unless otherwise noted				
Mount Type	Flush Mount			2) All tolerances are \pm 0.15 mm unless otherwise noted				
Storage Temperature	-30 ∼ +70	°C		3) All parts meet RoHS				
Operating Temperature	-20 ~ +60	°C		4) Subject to change or redrawn without notice				
Weight	1.5	g						