



		1		
Part Number:	1108-1	DRAWN	7/9/2020	
CMA		CJ		
20015		CHECKED	7/9/2020	
		P.D.	7/9/2020	
Description:	of Speaker	APPROVED	7/0/2020	
waterpro		J.S.	7/9/2020	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior writter permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




Side View




Bottom View





Side View (2)



	Items	Specifications	Conditions		'			
	Sound Pressure Level	81	dB (@ 0.25W/10cm), In 0.5cc chamber					
	Resonant Frequency	1,100	Hz, In 0.5cc chamber					
	Frequency Range	1,100 ~ 10,000	Hz, In 0.5cc chamber					
	Nominal Power	0.25	W, In 0.5cc chamber	REVISION HISTORY				
	Max. Power	0.5	W, In 0.5cc chamber	REV	DESCRIPTION	DATE	APPROVED	
^	Impedance	8	Ω		Released from Engineering	7/9/2020	J.S.	
	Cone Material	PEEK		NOTES				
	Mount Type	Flush Mount		All dimensions are in mm unless otherwise noted				
	IP Rating	IPX7		2) All tolerances are ± 0.2 mm unless otherwise noted				
	Storage Temperature	-40 ~ +85	°C	3) All parts meet RoHS				
	Operating Temperature	-20 ~ +70	°C	4) Subject to change or redrawn without notice				
	4 J 3 Additional considerations can be found at www.dbunlimitedco.com/technical-article							