



			1		
	Part Number:		DRAWN	2/10/2017	
	CM20	2000 1	CJ	3/10/2017	
	SW200	1908-1	CHECKED	10/2/2017	
			P.D.		
	Description:	namic Speaker	APPROVED	10/2/2017	
	Waterproof Dy		C.E.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Items	Specifications	Conditions		<u> </u>			
Sound Pressure Level	90	dB (@ 10cm), Avg.					
Resonant Frequency	1,200	Hz	 - -3- -				
Frequency Range	1,200 ~ 10,000	~ 10,000 Hz			REVISION HISTORY		
Nominal Power	1	W	REV	DESCRIPTION	DATE	APPROVED	
Max. Power	1.5	W		Released from Engineering	10/2/2017	C.E.	
Impedance	8	Ω	1	Updated resonant frequency, range, frame height, bottom	5/4/2018	C.E.	
Cone Material	Mylar			view detail			
Mount Type	Flush Mount		NOTES				
IP Rating	IP67		All dimensions are in mm unless otherwise noted				

IP Rating IP67 1) All dimensions are in mm unless otherwise noted Storage Temperature -20 ~ +55 °C 2) All tolerances are ± 0.3 mm unless otherwise noted Operating Temperature -20 ~ +55 °C 3) All parts meet RoHS

Weight 2.92 9 4) Subject to change or redrawn without notice