


TOP VIEW



SIDE VIEW



BOTTOM VIEW



	Specifications		Notes		Revision History						
Description	Value	Unit			Version	Description			Date	Approved	
Shape	Round		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			2/5/2014	J.S.	
Resonant Frequency	1,000	(Hz)	2) All parts meet RoHS								
Frequency Range	1,000 ~ 5,000	(Hz)	7								
SPL @ 10cm	88	(dBA)									
Impedance	8	(Ohm)	1								
Cone Material	Mylar										
Nominal Power	0.5	(W)									
Max Power	1.0	(W)									
Mount Type	Flush Mount				Drawn by	Date	Checked by	Date	Approved by	Date	
Operating Temperature	-30 ~ +60	°C			G.W.	1/27/2014	C.E.	2/4/2014	J.S.	2/5/2014	
Storage Temperature	-30 ~ +60	°C		Dunamic Speaker	Dimamia Spaakar		SM171008-1				
Weight	1.4	(g)		Dynamic Speaker		JINIT\ T009-T					

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.