


		1		
Part Number:		DRAWN	12/2/2016	
CMAE	0204-1	CJ		
5 45(CHECKED	12/2/2016	
		P.D.		
Description:	Speaker	APPROVED	12/2/2016	
Dynamic		J.S.	12/2/2016	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




-20 ~ +60

Operating Temperature

Side View



Bottom View



Items	Specifications	Conditions						
Sound Pressure Level	88	dB (@ 10cm)						
Resonant Frequency	200	Hz		REVISION HISTORY				
Frequency Range	200 ~ 10,000	Hz	REV	DESCRIPTION	DATE	APPROVED		
Nominal Power	3	W		Released from Engineering	12/2/2016	J.S.		
Max. Power	5	W		NOTES				
Impedance	4	Ω		1) All dimensions are in mm unless otherwise noted				
Cone Material	Mylar			2) All tolerances are ± 0.5 mm unless otherwise noted				
Mount Type	Flange Mount			3) All parts meet RoHS				
Storage Temperature	-30 ~ +70	°C	4) Subject to change or redrawn without notice					

4 **A** 2

°C