



Part Number:		DRAWN	2/24/2017	
CM/100	0204 1	CJ	3/24/2017	
SW1000304-1		CHECKED	10/6/2017	
		P.D.	10/6/2017	
Description:		APPROVED		
Waterproof Dy	namic Speaker	C.E.	10/6/2017	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View




## Side View (1)



## Side View (2)



## **Bottom View**



Items	Specifications	Conditions	REVISION HISTORY					
Sound Pressure Level	106	dB (@ 10cm), Avg.	REV	DESCRIPTION	DATE	APPROVED		
Resonant Frequency	350	Hz		Released from Engineering	10/6/2017	C.E.		
Frequency Range	350 ~ 20,000	Hz	1	Add polarity marking, remove connector	10/24/2017	C.E.		
Nominal Power	3	W	2	Update markings	2/28/2018	C.E.		
Max. Power	5	W	3	Updated tolerances	6/11/2018	C.E.		
Impedance	4	Ω	4	Updated dimensions, SPL	8/9/2018	C.E.		
Cone Material	Mylar		NOTES					
Mount Type	Frame Mount			1) All dimensions are in mm unless otherwise noted				
IP Rating	IP67			2) All tolerances are ± 0.5 mm unless otherwise noted				
Storage Temperature	-20 ~ +55	°C		3) All parts meet RoHS				
Operating Temperature	-20 ~ +55	°C	4) Subject to change or redrawn without notice					