



			1		
	Part Number:		DRAWN	4/5/2021	
	CM20	0508-2	CJ	4/5/2021	
	SIMZ80		CHECKED	4/5/2021	
			P.D.		
	Description:	c Speaker	APPROVED	4/5/2021	
	Dynamic		J.S.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



Items	Specifications	Conditions					
Sound Pressure Level	92	dB (@ 10cm)					
Resonant Frequency	550	Hz					
Frequency Range	550 ~ 9,000	Hz	REVISION HISTORY				
Nominal Power	1.5	W	REV	DESCRIPTION	DATE	APPROVED	
Max. Power	3.0	W		Released from Engineering	2/5/2014	J.S.	
Impedance	8	Ω	1	Revised cone material to paper, updated to new template	4/5/2021	J.S.	
Cone Material	Paper			NOTES			
Mount Type	Lead Wires			1) All dimensions are in mm unless otherwise noted			
Storage Temperature	-30 ~ +60	°C		2) All tolerances are ± 0.5 mm unless otherwise noted			
Operating Temperature	-20 ~ +60	°C		3) All parts meet RoHS			
Weight	8.7	g	4) Subject to change or redrawn without notice				