


			1	
	Part Number:	1308-2	DRAWN	7/9/2020
	CMAA		CJ	
	SWIZ		CHECKED	7/9/2020
			P.D.	
	Description:	of Speaker	APPROVED	7/9/2020
	Waterpro		J.S.	


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Suggested Pad Layout


Top View








Bottom View



Side View (2)



_	- -

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.

- 1					0			
	Items	Specifications	Conditions					
	Sound Pressure Level	89	dB (@ 0.4W/10cm), In 2cc chamber					
	Resonant Frequency	1,300	Hz, In 2cc chamber					
	Frequency Range	1,300 ~ 20,000	Hz, In 2cc chamber	REVISION HISTORY				
	Nominal Power	0.4	W, In 2cc chamber	REV	DESCRIPTION	DATE	APPROVED	
	Max. Power	0.6	W, In 2cc chamber		Released from Engineering	7/9/2020	J.S.	
^	Impedance	8	Ω	NOTES				
	Cone Material	PEEK		All dimensions are in mm unless otherwise noted				
	Mount Type	Flush Mount			2) All tolerances are ± 0.2 mm unless otherwise noted			
	IP Rating	IPX8		3) All parts meet RoHS				
	Storage Temperature	-30 ~ +70	°C	4) Subject to change or redrawn without notice				
	Operating Temperature	-20 ~ +60	°C					