


TOP VIEW



SIDE VIEW



BOTTOM VIEW



:	Specifications		Notes			Revision History					
Description	Value	Unit	Notes		Version	Description			Date	Approved	
Shape	Round		1) All dimensions are in mm u	1	Released from Engineering			2/5/2014	J.S.		
Resonant Frequency	550	(Hz)	2) All parts meet RoHS								
Frequency Range	550 ~ 7,000	(Hz)									
SPL @ 10cm	90	(dBA)									
Impedance	8	(Ohm)									
Cone Material	Polyetherimide										
Nominal Power	0.5	(W)									
Max Power	0.7	(W)									
Mount Type	Flush Mount				Drawn by	Date	Checked by	Date	Approved by	Date	
Operating Temperature	-20 ~ +80	°C			G.W.	1/27/2014	C.E.	2/4/2014	J.S.	2/5/2014	
Storage Temperature	-30 ~ +80	°C		High Temp Dynamic Speaker		SM280508-3					
Weight	5.7	(g)									