



		1		
Part Number:		DRAWN	0/4/2040	
CMAE	0508-1	CJ	8/1/2018	
5M450		CHECKED	8/1/2018	
		C.H.		
Description:	ic Speaker	APPROVED	8/1/2018	
Dynamic		C.E.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Items	Specifications	Conditions					
Sound Pressure Level	102	dB (@ 10cm), Avg.					
Resonant Frequency	500	Hz		REVISION HISTORY			
Frequency Range	500 ~ 6,000	Hz	REV	DESCRIPTION	DATE	APPROVED	
Nominal Power	1	W		Released from Engineering	2/5/2014	J.S.	
Max. Power	2	W	1	Updated to new drawing template and SPL	8/1/2018	C.E.	
Impedance	8	Ω		NOTES			
Cone Material	Mylar			All dimensions are in mm unless otherwise noted			
Mount Type	Flush Mount			2) All tolerances are ± 0.3 mm unless otherwise noted			
Storage Temperature	-30 ~ +60	°C		3) All parts meet RoHS			
Operating Temperature	-20 ~ +60	°C		Subject to change or redrawn without notice			
Weight	10.2	g					