


Part Number:		DRAWN	2/12/2017	
CMAO	1404-1	CJ	3/13/2017	
500 4 0.		CHECKED	10/2/2017	
		P.D.	10/2/2017	
Description:		APPROVED		
Waterproof Dy	namic Speaker	C.E.	10/2/2017	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View




-40 ~ +70

5.21


Operating Temperature

Weight

Side View



Bottom View



4) Subject to change or redrawn without notice

Items	Specifications	Conditions	REVISION HISTORY				
Sound Pressure Level	97	dB (@ 10cm), Avg.	REV	DESCRIPTION	DATE	APPROVED	
Resonant Frequency	1,400	Hz		Released from Engineering	10/2/2017	C.E.	
Frequency Range	300 ~ 10,000	Hz	1	Updated frequency range	12/27/2017	C.E.	
Nominal Power	2	W	2	Update markings	2/28/2018	C.E.	
Max. Power	3	W	3	Updated to show polarity	3/13/2019	C.E.	
Impedance	4	Ω	4	Updated temperatures	4/7/2020	P.D.	
Cone Material	Mylar		NOTES				
Mount Type	Frame Mount		1) All dimensions are in mm unless otherwise noted				
IP Rating	IP67		2) All tolerances are ± 0.2 mm unless otherwise noted				
Storage Temperature -40 ~ +70 °C 3) All parts meet RoHS							