


TOP VIEW



SIDE VIEW



BOTTOM VIEW



:	Specifications		Notes		Revision History					
Description	Value	Unit			Version	Description			Date	Approved
Shape	Round		1) All dimensions are in mm	1	Released from Engineering			2/8/2014	J.S.	
Resonant Frequency	600	(Hz)	2) All parts meet RoHS							
Frequency Range	600 ~ 20,000	(Hz)								
SPL @ 10cm	96	(dBA)								
Impedance	8	(Ohm)								
Cone Material	Mylar									
Nominal Power	0.3	(W)								
Max Power	0.5	(W)								
Mount Type	Flange Mount				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-10 ~ +40	°C			G.W.	1/27/2014	C.E.	2/4/2014	J.S.	2/8/2014
Storage Temperature	-20 ~ +60	°C		Dunamia Spaakar		SM300608-1				
Weight	6.9	(g)		Dynamic Speaker		21A120000-T				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.