

			1		
	Part Number:	0808-5	DRAWN	6/0/2017	
	CN110		CJ	6/8/2017	
	214190		CHECKED	10/2/2017	
			P.D.		
	Description:  Dynamic	c Speaker	APPROVED	10/2/2017	
			C.E.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View

13 ± 0.1-


10.8 ± 0.1-

-15.8 ± 0.1

Side View



**Bottom View** 



Items	Specifications	Conditions						
Sound Pressure Level	94	dB (@ 10cm)						
Resonant Frequency	850	Hz	REVISION HISTORY					
Frequency Range	850 ~ 10,000	Hz	REV	DESCRIPTION	DATE	APPROVED		
Nominal Power	1	W		Released from Engineering	10/2/2017	C.E.		
Max. Power	1.3	W	1	Updated drawing, specs	4/11/2018	C.E.		
Impedance	8	Ω		NOTES				
Cone Material	Polymer			All dimensions are in mm unless otherwise noted				
Mount Type	Flush Mount			2) All tolerances are ± 0.2 mm unless otherwise noted				
Storage Temperature	-40 ~ +85	°C		3) All parts meet RoHS				
Operating Temperature	-30 ~ +70	°C		Subject to change or redrawn without notice				
Weight	2.25	a						