


TOP VIEW



SIDE VIEW



BOTTOM VIEW



	Specifications		Notes			Revision History					
Description	Value	Unit]	Version	Description			Date	Approved		
Shape	Round		1) All dimensions are in mm u	1	Released from Engineering			2/5/2014	J.S.		
Resonant Frequency	600	(Hz)	2) All parts meet RoHS								
Frequency Range	600 ~ 6,500	(Hz)									
SPL @ 10cm	91	(dBA)									
Impedance	32	(Ohm)									
Cone Material	Mylar										
Nominal Power	0.25	(W)									
Max Power	0.5	(W)									
Mount Type	Flush Mount				Drawn by	Date	Checked by	Date	Approved by	Date	
Operating Temperature	-20 ~ +85	°C			G.W.	1/27/2014	C.E.	2/4/2014	J.S.	2/5/2014	
Storage Temperature	-30 ~ +85	°C		High Temp Dynamic Speaker		SM280632-1					
Weight	4.5	(g)									

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.