


			1		
	Part Number:		DRAWN	2/10/2017	
	CM20	0E00 1	CJ	3/10/2017	
	SW200	7208-1	CHECKED	10/2/2017	
			P.D.		
	Description:	namic Speaker	APPROVED	10/2/2017	
	Waterproof Dy		C.E.		


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Bottom View

Top View



Side View



	Items	Specifications	Conditions					
	Sound Pressure Level	85	dB (@ 10cm), Avg.		REVISION HISTORY			
	Resonant Frequency	800	Hz	REV	DESCRIPTION	DATE	APPROVED	
	Frequency Range	800 ~ 10,000	Hz		Released from Engineering	10/2/2017	C.E.	
	Nominal Power	1.5	W	1	Update markings	2/28/2018	C.E.	
	Max. Power	2	W	2	Update resonant freq, range, and add detail on bottom	5/4/2018	C.E.	
	Impedance	8	Ω	7 -	view			
A .	Cone Material	PU + PEI			NOTES			
	Mount Type	Flush Mount			All dimensions are in mm unless otherwise noted			
	IP Rating	IP67			2) All tolerances are ± 0.2 mm unless otherwise noted			
	Storage Temperature	-20 ~ +55	°C		3) All parts meet RoHS			
	Operating Temperature	-20 ~ +55	°C		4) Subject to change or redrawn without notice			
	Weight	4.02	g					
	4 3 4 2 1 1 Additional considerations can be found at www.dbunlimitedco.com/technical-articles.							