



		1		
Part Number:		DRAWN	4/15/2016	
SC570708-1		CJ	4/15/2016	
SC5/(7/08-1	CHECKED	4/18/2016	
		P.D.	4/10/2010	
Description:	c Speaker	APPROVED	4/18/2016	
Dynami		J.S.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Г	Items	Specifications	Conditions				
Г	Sound Pressure Level	98	dB (@ 10cm)	REVISION HISTORY			
Г	Resonant Frequency	700	Hz	REV	DESCRIPTION	DATE	APPROVED
A	Frequency Range	700 ~ 20,000	Hz		Released from Engineering	12/11/2013	J.S.
	Nominal Power	2	W	1	Updated to new template	4/18/2016	J.S.
	Max. Power	3	W	2	Updated to new template, frequency range, dimensions	1/3/2018	C.E.
	Impedance	8	Ω		NOTES		
	Cone Material	Cloth		All dimensions are in mm unless otherwise noted			
	Mount Type	Flange Mount		2) All tolerances are \pm 0.5 mm unless otherwise noted			

 Storage Temperature
 -30 ~ +70
 °C
 3) All parts meet RoHS

 Operating Temperature
 -20 ~ +60
 °C
 4) Subject to change or redrawn without notice

 Weight
 13.7
 9

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.