


TOP VIEW



SIDE VIEW



BOTTOM VIEW



| | Specifications | | Notes | | | Revision History | | | | | |
|-----------------------|--------------------------|-------|---|---------------------------|----------|---------------------------|------------|----------|-------------|----------|--|
| Description | Value | Unit | Notes 1) All dimensions are in mm unless otherwise noted | | Version | Description | | | Date | Approved | |
| Shape | Round | | | | 1 | Released from Engineering | | | 2/5/2014 | J.S. | |
| Resonant Frequency | 880 | (Hz) | 2) All parts meet RoHS | | | | | | | | |
| Frequency Range | 880 ~ 20,000 | (Hz) | | | | | | | | | |
| SPL @ 10cm | 85 | (dBA) | | | | | | | | | |
| Impedance | 16 | (Ohm) | | | | | | | | | |
| Cone Material | Polyethylene Naphthalate | | | | | | | | | | |
| Nominal Power | 0.3 | (W) | | | | | | | | | |
| Max Power | 0.6 | (W) | | | | | | | | | |
| Mount Type | Flush Mount | | | | Drawn by | Date | Checked by | Date | Approved by | Date | |
| Operating Temperature | -30 ~ +80 | °C | | | G.W. | 1/27/2014 | C.E. | 2/4/2014 | J.S. | 2/5/2014 | |
| Storage Temperature | -30 ~ +80 | °C | | High Temp Dynamic Speaker | | SM160816-1 | | | | | |
| Weight | 1 | (g) | | | | 2IAITOOQTO-T | | | | | |

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.