


		1		
Part Number:		DRAWN		
CM1E	0808-9	CJ	5/30/2018	
DIAITO		CHECKED	5/30/2018	
		C.H.		
Description:	Speaker	APPROVED	5/30/2018	
Dynamic		C.E.		


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Bottom View

Top View



Side View



	Items	Specifications	Conditions						
	Sound Pressure Level	92	dB (@ 10cm)						
	Resonant Frequency	850	Hz						
	Frequency Range	500 ~ 10,000	Hz	1					
	Nominal Power	0.7	W	REVISION HISTORY					
	Max. Power	1	W	REV	DESCRIPTION	DATE	APPROVED		
,	Impedance	8	Ω		Released from Engineering	5/30/2018	C.E.		
^	Cone Material	Polymer		NOTES					
	Mount Type	Flush Mount		All dimensions are in mm unless otherwise noted					
	IP Rating	IPX7		2) All tolerances are ± 0.2 mm unless otherwise noted					
	Storage Temperature	-40 ~ +85	°C	3) All parts meet RoHS					
	Operating Temperature	-30 ~ +70	°C	4) Subject to change or redrawn without notice					
	Weight	1.6	g						
	4 3 4 2 1 1 Additional considerations can be found at www.dbunlimitedco.com/technical-articles.								