



			1		
	Part Number:		DRAWN	6/14/2016	
	CNAFO	0308-1	CJ	6/14/2016	
	5141201		CHECKED	6/14/2016	
			P.D.		
	Description:	c Speaker	APPROVED	6/14/2016	
	Dynamic		J.S.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



Items	Specifications	Conditions					
Sound Pressure Level	92	dB (@ 10cm)		REVISION HISTORY			
Resonant Frequency	350	Hz	REV	DESCRIPTION	DATE	APPROVED	
Frequency Range	350 ~ 20,000	Hz		Released from Engineering	2/8/2014	J.S.	
Nominal Power	1	W	1	Updated to new template	6/14/2016	J.S.	
Max. Power	1.5	W	2	Corrected released from engineering information	11/7/2017	C.E.	
Impedance	8	Ω		NOTES			
Cone Material	Mylar			1) All dimensions are in mm unless otherwise noted			
Mount Type	Flush Mount			2) All tolerances are $\pm$ 0.5 mm unless otherwise noted			
Storage Temperature	-30 ~ +60	%		3) All parts meet RoHS			
Operating Temperature	-30 or ±60	oC		4) Subject to change or redrawn without notice			