TOP VIEW SIDE VIEW 70±0.5 63±0.5 63±0.5 70±0.5 70±0.5 63±0.5 70

Specifications			Notes		Revision History					
Description	Value	Unit	Notes		Version	Description		Date	Approved	
Shape	Rectangle		1) All dimensions are in mm u	1	Released from Engineering			2/5/2014	J.S.	
Resonant Frequency	300	(Hz)	2) All parts meet RoHS							
Frequency Range	200 ~ 20,000	(Hz)								
SPL @ 10cm	100	(dBA)								
Impedance	8	(Ohm)								
Cone Material	Cloth									
Nominal Power	2	(W)								
Max Power	5	(W)								
Mount Type	Frame Mount				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-40 ~ +80	°C			G.W.	1/27/2014	C.E.	2/5/2014	J.S.	2/5/2014
Storage Temperature	-40 ~ +80	°C		High Temp Dynamic Speaker		SC700308-1				
Weight	7.6	(g)								

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.