

SIDE VIEW



BOTTOM VIEW



Specifications			Notes		Revision History					
Description	Value	Unit	1) All dimensions are in mm unless otherwise noted		Version	Description		Date	Approved	
Shape	Round				1	Released from Engineering			2/5/2014	J.S.
Resonant Frequency	600	(Hz)	2) All parts meet RoHS							
Frequency Range	600 ~ 6,000	(Hz)								
SPL @ 10cm	92	(dBA)								
Impedance	8	(Ohm)		_						
Cone Material	Mylar									
Nominal Power	0.5	(W)								
Max Power	0.8	(W)								
Mount Type	Flush Mount				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-20 ~ +60	°C			G.W.	1/27/2014	C.E.	2/4/2014	J.S.	2/5/2014
Storage Temperature	-30 ~ +60	°C		Dynamic Speaker		SM400608-2				
Weight	9.2	(g)								