


STRUCTURE (构造)				
NO.	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	印字: E488937 UL20624 (43μm)		
		白膜: 80°C 60V (43μm)		
2	SUPPORTING TAPE (补强板)	225μm	Blue (蓝色)	
3	CONDUCTOR (导体)	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.3	±0.03
CONDUCTOR (导体镀层)	PLATED (电镀)	锡Sn (1μm)	MIN	
	PLATED (电镀)			

DIMENSION (尺寸)				
No. of conductors (导体数目)	N	16		
Pitch (间距)	P	0.5	±0.05	
Span (总间距)	SP	7.5	±0.05	
Width (总宽度)	W	8.5	±0.08	
Margin (边缘宽度)	M	0.5	±0.07	
Total length (总长度)	TL	65	±2.0	
Insert Thickness (插接端厚度)	T	0.3	±0.03	
Surface Thickness (线身厚度)	ST	0.12	±0.03	
Strip Length (裸铜长度)	S1	4.0	±1.0	
	S2	4.0	±1.0	
Supporting Tape Length (补强板长度)	B1	8.0	±2.0	
	B2	8.0	±2.0	



技术要求:
 1、保存环境:
 温度: 15~25°C 湿度: 30~50RH%
 2、保质期:
 镀金: 12个月 镀锡: 6个月
 3、产品符合RoHS 2.0标准

Customer P/N: (客户料号):			C14435				深圳市连线电子有限公司			
NO.	DESCRIPTION (描述)	DATE	Drawing: (绘制)	Kent		Title: FPC CABLE				
0	NEW DRAWING (新作成)	2024. 04. 03	Check: (审核)			Customer (客户)		A771	Rev. (版次)	A/0
			Approved: (核准)			Dwg NO. (图纸编码)			Page (页码)	1/1
			Unit: mm						Weight (重量)	