


- SPECIFICATIONS
1. Current Rating: 2A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO(2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2AW-PF	2.00	6.00
3	XD-HY-3AW-PF	4.00	8.00
4	XD-HY-4AW-PF	6.00	10.00
5	XD-HY-5AW-PF	8.00	12.00
6	XD-HY-6AW-PF	10.00	14.00
7	XD-HY-7AW-PF	12.00	16.00
8	XD-HY-8AW-PF	14.00	18.00
9	XD-HY-9AW-PF	16.00	20.00
10	XD-HY-10AW-PF	18.00	22.00
11	XD-HY-11AW-PF	20.00	24.00
12	XD-HY-12AW-PF	22.00	26.00
13	XD-HY-13AW-PF	24.00	28.00
14	XD-HY-14AW-PF	26.00	30.00
15	XD-HY-15AW-PF	28.00	32.00
16	XD-HY-16AW-PF	30.00	34.00

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-HY-NAW-PF	单位 UNITS	mm
			X.XX ±0.20	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10						
1	初版发行		Angle ±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							