


- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XH-2A-R	2.50	7.50
3	XD-XH-3A-R	5.00	10.00
4	XD-XH-4A-R	7.50	12.50
5	XD-XH-5A-R	10.00	15.00
6	XD-XH-6A-R	12.50	17.50
7	XD-XH-7A-R	15.00	20.00
8	XD-XH-8A-R	17.50	22.50
9	XD-XH-9A-R	20.00	25.00
10	XD-XH-10A-R	22.50	27.50
11	XD-XH-11A-R	25.00	30.00
12	XD-XH-12A-R	27.50	32.50
13	XD-XH-13A-R	30.00	35.00
14	XD-XH-14A-R	32.50	37.50
15	XD-XH-15A-R	35.00	40.00
16	XD-XH-16A-R	37.50	42.50



GENERAL TOLERANCE		制图	10
DIM TOL		DRAWING	
X.X ±0.30		审核	
X.XX ±0.20		CHECK	
X.XXX ±0.10		批准	
Angle ±3.0°		APPROVAL	
投影		比例	
		SCALE	
		材料	
		MATERIAL	

XD 深圳讯答科技有限公司
ShenzhenXunDaTechnology Co.,Ltd

产品名称 TITLE	XH (2.50) 单排 直针 红色	版本 REV.	A
产品料号 PART NO.	XD-XH-NA-R	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE
1	初版发行	