


SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer Nylon66 UL94-VO(2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2AW-L	2.00	6.00
3	XD-HY-3AW-L	4.00	8.00
4	XD-HY-4AW-L	6.00	10.00
5	XD-HY-5AW-L	8.00	12.00
6	XD-HY-6AW-L	10.00	14.00
7	XD-HY-7AW-L	12.00	16.00
8	XD-HY-8AW-L	14.00	18.00
9	XD-HY-9AW-L	16.00	20.00
10	XD-HY-10AW-L	18.00	22.00
11	XD-HY-11AW-L	20.00	24.00
12	XD-HY-12AW-L	22.00	26.00
13	XD-HY-13AW-L	24.00	28.00
14	XD-HY-14AW-L	26.00	30.00
15	XD-HY-15AW-L	28.00	32.00
16	XD-HY-16AW-L	30.00	34.00

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	HY (2.00) 单排带扣 弯针 蓝色	版本 REV.	A
			X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-HY-NAW-L	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							