



	0.12
	0.12

SECTION:M-M



RECOMMEND PCB LAYOUT

■ SPECIFICATIONS

- Voltage rating:125V AC/DC
- Current rating: 1A, AC/DC
- Withstanding Voltage:500V AC/minute
- Insulation resistance:1000MΩ min
- Temperature range:-40°Cto+105°C
- Contact resistance:20mΩ max

■ WAFER

- Part No:CS-1147H-14
- Poles:2-16
- Material:LCP UL94V-0, Natural
- Contact and metal Hold-down: Brass
- Plating: Tin plated
- Q' TY: 2000 pcs/tape reel

Poles	PART NO	DIMENSION (mm)		
		A	B	C
2	CS-1147H-02	1.25	4.25	7.35
3	CS-1147H-03	2.50	5.50	8.60
4	CS-1147H-04	3.75	6.75	9.85
5	CS-1147H-05	5.00	8.00	11.10
6	CS-1147H-06	6.25	9.25	12.35
7	CS-1147H-07	7.50	10.50	13.60
8	CS-1147H-08	8.75	11.75	14.85
9	CS-1147H-09	10.00	13.00	16.10
10	CS-1147H-10	11.25	14.25	17.35
11	CS-1147H-11	12.50	15.50	18.60
12	CS-1147H-12	13.75	16.75	19.85
13	CS-1147H-13	15.00	18.00	21.10
14	CS-1147H-14	16.25	19.25	22.35
15	CS-1147H-15	17.50	20.50	23.60
16	CS-1147H-16	18.75	21.75	24.85

ROHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.

类别	WAFFER	品名	CS-1147H-14	X.	±0.50	材料		单位	mm	SHEET 1 OF 1			
	版本	A/1	设计	李文畅	X.X	±0.40	颜色		比例	1:1		修改内容	修改日期
	制定部门	工程课	绘制	李文畅	X.XX	±0.30	画法		数量				
	工程图号	CST-001147H	审核	姚培柱	X.XXX	±0.20	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.						
	制定日期	2017-08-10	核准	韦栋释	X.XXXX	±0.10							